



Main

Range	Sequence5
Product or component type	Keycard switch
Device presentation	Complete product
Switch additional information	With internal power connection
Switch application	On/Off switching
Colour tint	Black
Type of packing	Box
Quantity per set	Set of 1
Sale per indivisible quantity	1
Light source	Blue LED - 0.15 mA
Number of terminals	2 screw terminals

Complementary

Device mounting	Flush
Switch function	1-way
Contacts type and composition	1 NO
Actuator	Card
Fixing mode	By screws
Surface finish	Matt
Rated current	10 AX - 250 V +/- 10 % AC 50 Hz
Minimum load breaking capacity	200 operations 1.25 I _n and 1.1 U _n with cos φ = 0.3
Service life in cycles	20000 cycles ON and OFF at rated voltage with cos φ = 0.6
Number of cables	1 x 1.5 mm ² 2 x 2.5 mm ²
Cable stiffness	Flexible Solid Stranded
Wire stripping length	12 mm
Material	Metal
Height	80 mm
Width	80 mm
Depth	38 mm

Embedding depth	27 mm
Product weight	0.625 kg

Environment

Dielectric strength	2000 V
Standards	2006/95/EEC EN 60669-1
Product certifications	NF N LCIE : NF 619318A
Ambient air temperature for operation	5...35 °C
Ambient air temperature for storage	-5...50 °C
IK degree of protection	IK04
IP degree of protection	IP21 D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free