



Main

Range of product	Sequence5
Product or component type	TV single shield
Device presentation	Complete product
Type of packing	Box
Quantity per set	Set of 1
Sale per indivisible quantity	1

Complementary

Device mounting	Flush
TV connector	Male IEC 9.52 mm
Path attenuation	1.5 dB for TV signal @ 5...1800 MHz 2.5 dB for TV signal @ 1800...2150 MHz
Fixing mode	By screws
Colour tint	Nickel
Surface finish	Glossy
Connections - terminals	Screw
Shape of screw head	Pozidriv No 1
Wire stripping length	8 mm
Type of cable	Coaxial
Cable outer diameter	7 mm
Material	Metal
Height	80 mm
Width	80 mm
Depth	27 mm
Embedding depth	25 mm
Product weight	0.214 kg

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	EN 50083-4

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Liquid soap Alcohol UV resistant Petrol Window-cleaning fluid Acetone Oil Ammonia Bleach
Environmental health and issues	Halogen free