



Main

Range of product	Sequence5
Product or component type	TV/SAT/R socket
Device presentation	Complete product
Type of packing	Box
Quantity per set	Set of 1
Sale per indivisible quantity	1

Complementary

Device mounting	Flush
TV connector	Male IEC 9.52 mm
Radio connector	Female IEC 9.52 mm
SAT connector	F type
Branch attenuation	<= 3 dB for SAT signal @ 950...2400 MHz <= 3 dB for TV signal @ 125...862 MHz <= 2.5 dB for R signal @ 5...108 MHz
Return loss	>= 10 dB for IN-OUT signal >= 10 dB for TV signal >= 12 dB for R signal >= 10 dB for SAT signal
DC current flow	In SAT socket
Fixing mode	By screws
Colour tint	Bronze
Surface finish	Glossy
Rated current	350 mA - 24 V DC
Connections - terminals	Screw
Shape of screw head	Pozidriv No 1
Wire stripping length	8 mm
Type of cable	Coaxial
Cable outer diameter	7 mm
Material	Metal
Height	80 mm
Width	80 mm
Depth	39 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Embedding depth	31 mm
Product weight	0.231 kg

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	EN 50083-4
IK degree of protection	IK04
IP degree of protection	IP21 D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free