



Main

| | |
|-------------------------------|------------------|
| Range of product | Sequence5 |
| Product or component type | TV/SAT/R socket |
| Device presentation | Complete product |
| Type of packing | Box |
| Quantity per set | Set of 1 |
| Sale per indivisible quantity | 1 |

Complementary

| | |
|-------------------------|--|
| Device mounting | Flush |
| TV connector | Male IEC 9.52 mm |
| Radio connector | Female IEC 9.52 mm |
| SAT connector | F type |
| Branch attenuation | <= 3 dB for SAT signal @ 950...2400 MHz <= 3 dB for TV signal @ 125...862 MHz <= 2.5 dB for R signal @ 5...108 MHz |
| Return loss | >= 10 dB for IN-OUT signal >= 10 dB for TV signal >= 12 dB for R signal >= 10 dB for SAT signal |
| DC current flow | In SAT socket |
| Fixing mode | By screws |
| Colour tint | Black |
| Surface finish | Matt |
| Rated current | 350 mA - 24 V DC |
| Connections - terminals | Screw |
| Shape of screw head | Pozidriv No 1 |
| Wire stripping length | 8 mm |
| Type of cable | Coaxial |
| Cable outer diameter | 7 mm |
| Material | Metal |
| Height | 80 mm |
| Width | 80 mm |
| Depth | 39 mm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-----------------|----------|
| Embedding depth | 31 mm |
| Product weight | 0.231 kg |

Environment

| | |
|---------------------------------------|--|
| Ambient air temperature for storage | -5...50 °C |
| Ambient air temperature for operation | 5...45 °C |
| Standards | EN 50083-4 |
| IK degree of protection | IK04 |
| IP degree of protection | IP21 D |
| Environmental characteristic | Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid |
| Environmental health and issues | Halogen free |