



Main

Range of product	Sequence5
Product or component type	Audio socket
Connector type	HD15 VGA Mini-jack
Device presentation	Mechanism
Socket number	2
Quantity per set	Set of 1
Sale per indivisible quantity	1

Complementary

Device mounting	Flush
Fixing mode	By screws
Colour tint	Brushed gold
Surface finish	Glossy
Material	Metal
Height	80 mm
Width	80 mm
Depth	26 mm
Embedding depth	19 mm
Product weight	0.176 kg

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...40 °C
Standards	UL 94 JIS H 3100 JIS G 3141 IEC 60512-13-2 IEC 60512-5-2 IEC 60998-1 IEC 60998-2-1
IP degree of protection	IP41
IK degree of protection	IK04

Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free
