



### Main

Range	Sequence5
Product or component type	Presence detector
Device presentation	Complete product
Type of packing	Box
Quantity per set	1 piece
Sale per indivisible quantity	1
Wiring device additional information	Manual override with push-buttons NC

### Complementary

Device mounting	Flush
Fixing mode	By screws
Colour tint	Copper
Surface finish	Glossy
Movement detection area	10 x 20 m (PIR mounting height 1.2 m)
Presence detection area	10 x 18 m (PIR mounting height 1.2 m)
Detection angle	112°
Selection modes	A: automatic M: manual
Light intensity adjustment	5...1000 lux
Wiring configuration	2-wire
Time delay	5 s...20 min
Load type	230 V AC incandescent lamp 40...350 W 230 V AC halogen lamp 40...350 W
[Ue] rated operational voltage	230 V AC 50 Hz
Protection type	Fuse protection
Number of pin in parallel	40 W for 1 PIR in parallel 50 W for 2 PIR in parallel 80 W for 3 PIR in parallel
Connected auxiliaries	Maximum 3 detectors in parallel for a load
Number of terminals	2 screw terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...2 x 2.5 mm <sup>2</sup> for solid cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> for stranded cable(s)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

	1 x 1.5...2 x 2.5 mm <sup>2</sup> for flexible cable(s)
Wire stripping length	8 mm
Material	Metal
Mounting height	1...1.4 m
Height	80 mm
Width	80 mm
Depth	47 mm
Embedding depth	43 mm
Net weight	0.232 kg

## Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...35 °C
Derating factor	With power derating 5 W per °C above 25 °C
Standards	2006/95/EEC EN 60669-2-1 2004/108/EC EN 61000-6-2
Product certifications	LCIE: CCA-SE_4179 N NF
IK degree of protection	IK04
IP degree of protection	IP20

## Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information