



Main

Range	Sequence5
Product or component type	Cable outlet
Device presentation	Complete product
Product specific application	Exit wire for electrical heating
Type of packing	Box
Quantity per set	Set of 1
Sale per indivisible quantity	1

Complementary

Device mounting	Flush
Rated current	16 A
Fixing mode	By screws
Colour tint	Copper
Surface finish	Glossy
Connections - terminals	Screw
Number of loop terminals	2
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...1 x 2.5 mm ² for rigid cable(s) 1 x 1.5...1 x 2.5 mm ² for flexible cable(s) 1 x 1.5...1 x 2.5 mm ² for stranded cable(s)
Cable outer diameter	6...12 mm
Wire stripping length	12 mm
Material	Metal
Height	80 mm
Width	80 mm
Depth	38 mm
Embedding depth	19 mm
Product weight	0.183 kg

Environment

Ambient air temperature for storage	-5...50 °C
-------------------------------------	------------

Ambient air temperature for operation	5...35 °C
Standards	UTE C 61-392 EN 60669-1
Product certifications	NF LCIE : NF 603415A
IK degree of protection	IK04
IP degree of protection	IP2xC
Environmental characteristic	Petrol Bleach Alcohol Oil Ammonia Acetone UV resistant Window-cleaning fluid Liquid soap
Environmental health and issues	Halogen free