



Main

Range	ARGUS
Product or component type	Occupancy sensor
Device application	Lighting
Load type	Energy saving lamp <= 80 VA Low voltage halogen lamp <= 1000 VA Incandescent lamp <= 2000 W Halogen lamp <= 1000 VA Fluorescent lamp 100 µF <= 900 VA

Complementary

Rated voltage	230 V +/- 10 % AC 50/60 Hz
Detection angle	360°
Presence detection area	PIR : 360°, 7 m
Device mounting	Surface
Mounting support	Ceiling
Mounting height	2...3 m
Diameter	121.5 mm
Depth	42.5 mm

Environment

Electrical shock protection class	Class II
IP degree of protection	IP40
Ambient air temperature for operation	0...45 °C
Standards	EN 60669-2-1 EN 60669-1

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant - since 1342 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available