



Main

Range	ARGUS
Product or component type	Occupancy sensor
Load type	Energy saving lamp <= 80 VA Low voltage halogen lamp <= 1000 VA Incandescent lamp <= 2000 W Halogen lamp <= 1000 VA Fluorescent lamp 100 µF <= 900 VA HVAC <= 5 A 30 V DC HVAC <= 5 A 250 V AC cos phi = 1 HVAC <= 1 A 250 V AC cos phi = 0.4

Complementary

Rated voltage	230 V +/- 10 % AC 50/60 Hz
Detection angle	360°
Presence detection area	PIR : 360°, 7 x 7 m
Device mounting	Surface
Mounting support	Ceiling
Mounting height	2...3 m
Diameter	120 mm
Depth	41 mm

Environment

Electrical shock protection class	Class II
IP degree of protection	IP20
Ambient air temperature for operation	0...45 °C
Standards	EN 60669-2-1 EN 60669-1

Contractual warranty

Warranty period	18 months
-----------------	-----------