



### Main

Range	ARGUS
Product or component type	Occupancy sensor
Load type	Energy saving lamp <= 80 VA Low voltage halogen lamp <= 1000 VA Incandescent lamp <= 2000 W Halogen lamp <= 1000 VA Fluorescent lamp 100 µF <= 900 VA HVAC <= 5 A 30 V DC HVAC <= 5 A 250 V AC cos phi = 1 HVAC <= 2 A 250 V AC cos phi = 0.4

### Complementary

Rated voltage	230 V +/- 10 % AC 50/60 Hz
Detection angle	360°
Presence detection area	PIR : 360°, 7 x 7 m
Device mounting	Flush
Mounting support	Ceiling
Mounting height	2...3 m
Diameter	Sensor : 80 mm
Height	Power box : 124 mm
Width	Power box : 66 mm
Depth	Sensor : 52 mm Power box : 37 mm

### Environment

Electrical shock protection class	Class II
IP degree of protection	Sensor IP40 Power box IP20
Ambient air temperature for operation	0...45 °C
Standards	EN 60669-2-1 EN 60669-1

### Contractual warranty

Warranty period	18 months
-----------------	-----------