



### Main

Range	ARGUS
Product or component type	Occupancy sensor
Load type	Energy saving lamp <= 80 VA LED lamp <= 200 W Incandescent lamp <= 2000 W 1-10 V ballast <= 100 mA Halogen lamp <= 1000 VA Low voltage halogen lamp with conventional transformer <= 1000 VA Low voltage halogen lamp with electronic transformer <= 1000 VA Fluorescent lamp <= 1000 VA HVAC <= 5 A 30 V DC HVAC <= 5 A 250 V AC cos phi = 1

### Complementary

Rated voltage	230 V +/- 10 % AC 50/60 Hz
Detection angle	360°
Presence detection area	PIR : 360°, 8 x 8 m
Device mounting	Flush Surface
Mounting support	Ceiling
Mounting height	2...3 m
Diameter	110 mm
Depth	62 mm

### Environment

Electrical shock protection class	Class II
IP degree of protection	IP40 flush mounting IP54 surface mounting
Ambient air temperature for operation	0...45 °C (indoor) -20...45 °C (outdoor)

### Contractual warranty

Warranty period	18 months
-----------------	-----------