



Main

Range	ARGUS
Product or component type	Occupancy sensor
Load type	Energy saving lamp <= 80 VA Low voltage halogen lamp <= 1000 VA Incandescent lamp <= 2000 W Halogen lamp <= 1000 VA Fluorescent lamp 100 µF <= 900 VA HVAC <= 5 A 30 V DC HVAC <= 10 A 250 V AC cos phi = 1

Complementary

Rated voltage	230 V +/- 10 % AC 50/60 Hz
Detection angle	180°
Presence detection area	PIR : 360°, 8 x 8 m US : 180°, 8 x 10 m
Device mounting	Flush Surface
Mounting support	Ceiling
Mounting height	2...3 m
Diameter	111.5 mm
Depth	72 mm surface mounted 90 mm flush mounting

Environment

Electrical shock protection class	Class II
IP degree of protection	IP20
Ambient air temperature for operation	0...45 °C
Standards	EN 61000-3-3 EN 61000-3-2 EN 60669-2-1 EN 60669-1 EN 55015 EN 61547 EN 55022

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty period	18 months
-----------------	-----------
