



Purchase

APC
 SBPAR30K40H-WP

Overview

Model Name	APC Parallel Maintenance Bypass Panel, up to 3 units 30-40kVA, 400V Wallmount
Includes	Installation guide , User Manual
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Andorra , United Arab Emirates , Afghanistan , Albania , Armenia , Angola , Austria , Australia , Azerbaijan , Bosnia And Herzegovina , Bangladesh , Belgium , Burkina Faso , Bulgaria , Bahrain , Burundi , Benin , Brunei Darussalam , Bhutan , Botswana , Belarus , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Central African Republic , Congo , Switzerland , Cote D'Ivoire , Cook Islands , Cameroon , China , Serbia And Montenegro , Cyprus , Czech Republic , Germany , Djibouti , Denmark , Algeria , Estonia , Egypt , Western Sahara , Spain , Finland , Fiji , France , Gabon , United Kingdom , Georgia , French Guiana , Ghana , Gibraltar , Gambia , Guinea , Guadeloupe , Equatorial Guinea , Greece , Hong Kong , Croatia , Hungary , Indonesia , Ireland , Israel , India , Iraq , Iran (Islamic Republic Of) , Iceland , Italy , Jordan , Japan , Kenya , KOREA, REPUBLIC OF , Kuwait , Cayman Islands , Kazakhstan , Lebanon , Liechtenstein , Sri Lanka , Liberia , Lesotho , Lithuania , Luxembourg , Latvia , Morocco , Moldova, Republic Of , Madagascar , Macedonia , Mali , Myanmar , Martinique , Mauritania , Malta , Mauritius , Malawi , Malaysia , Mozambique , Namibia , Niger , Nigeria , Netherlands , Norway , Nepal , New Zealand , Oman , Papua New Guinea , Philippines , Pakistan , Poland , Portugal , Reunion , Romania , Russian Federation , Rwanda , Saudi Arabia , Sudan , Sweden , Singapore , Slovenia , Slovakia (Slovak Republic) , Sierra Leone , Senegal , Somalia , Chad , Togo , Thailand , Turkmenistan , Tunisia , East Timor , Turkey , Taiwan , TANZANIA, UNITED REPUBLIC OF , Ukraine , Uganda , Uzbekistan , Viet Nam , Mayotte , South Africa , Zimbabwe

Output

Nominal Output Voltage	400V 3PH
Maximum Total Current Draw per Phase	182.400000 A
Output Connections	(1) Hard Wire 5-wire (3PH + N + G) (Battery Backup)

Input

Nominal Input Voltage	400V 3PH
Input Frequency	50 Hz
Maximum Input Current per phase	182.40000000000001 A

Physical

Net Weight	53 kg
Maximum Height	1174 mm
Maximum Width	560 mm
Maximum Depth	216 mm
Shipping Weight	55 kg
Shipping Height	1298 mm
Shipping Width	704 mm
Shipping Depth	335 mm

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-9000 meters

Conformance

Approvals	EN 50091-2 , EN/IEC 62040-3 , EN/IEC 62040-1-1 , VFI-SS-111
Standard warranty	1 year repair or replace