



Main

Range name	Sedna
Product or component type	Switch
Delivery form	Complete product
Cover plate color	Titanium
Function	1-pole
Type of packing	Blister
Rated current	10 AX - 250 V AC

Complementary

Installation	Flush
Height	80 mm
Power range	2300 W
Product weight	0.06043 kg
Depth	37 mm
Surface finish	Glossy
Width	85 mm
Fixing mode	Screws or claws, 51...70 mm
Terminal capacity	2 x 2.5 mm ²

Environment

IP degree of protection	IP20
Product certifications	TSE

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Reference not containing SVHC above the threshold

Product environmental profile

Available

 [Product Environmental Profile](#)

Product end of life instructions

Need no specific recycling operations
