



Main

Range name	Sedna
Product or component type	Switch
Delivery form	Complete product
Kind of terminals	Screwless terminals
Cover plate color	Cream
Function	1-pole 2-circuit
Rated current	10 AX - 250 V AC

Complementary

Installation	Flush
Height	80 mm
Material of visible parts	Thermoplastic ABS-UV stabilised
Power range	2300 W
Product weight	0.089 kg
Depth of visual part	12 mm
Wire structure	Flexible Rigid
Depth	37 mm
Surface finish	Glossy
Width	85 mm
Wire stripping length	13 mm
Fixing mode	Screws or claws, 51...70 mm
Terminal capacity	2 x 2.5 mm ²

Environment

IP degree of protection	IP20
Conformity mark	CE

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1715 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------