


Product data sheet

Specifications



Switch, Sedna, 1pole 2-circuits, 10AX, locator light, white

SDN0300321

⚠ Discontinued on: Dec 30, 2023

⚠ Discontinued

Main

| | |
|---------------------------|-----------------------------|
| Range | Sedna |
| Product Or Component Type | Switch |
| Device Presentation | Mechanism with fixing frame |
| Device Application | Control |
| Switch Function | 1-pole 2-circuit |
| Colour Tint | White |

Complementary

| | |
|--------------------------------|--|
| Device Mounting | Flush |
| Surface Finish | Glossy |
| Kind Of Terminals | Screwless terminals |
| Accessory / Separate Part Type | Claw and screw for mechanism |
| Power Range | 2300 W |
| Wire Structure | Flexible Rigid |
| Wire Stripping Length | 13 mm |
| Fixing Mode | Claws, span of claws working range: 51...70 mm Screws |
| Height | 71 mm |
| Width | 71 mm |
| Depth | 37 mm |
| Depth Of Visual Part | 12 mm |
| Net Weight | 0.058165 kg |
| Market Segment | Small commercial Residential |

Environment

| | |
|-------------------------|-------------|
| Ip Degree Of Protection | IP20 |
| Conformity Mark | CE |
| Product Certifications | GOST-R |
| Standards | IEC 60669-1 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.500 cm |
| Package 1 Width | 7.000 cm |
| Package 1 Length | 7.000 cm |
| Package 1 Weight | 60.000 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 9.500 cm |
| Package 2 Width | 18.500 cm |
| Package 2 Length | 27.500 cm |
| Package 2 Weight | 696.000 g |
| Unit Type Of Package 3 | S04 |
| Number Of Units In Package 3 | 120 |
| Package 3 Height | 30.000 cm |
| Package 3 Width | 40.000 cm |
| Package 3 Length | 60.000 cm |
| Package 3 Weight | 9.026 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |