



Main

| | |
|---------------------------|---------------------|
| Range name | Sedna |
| Range | Sedna |
| Device application | Control |
| Product or component type | Switch |
| Function | 1-pole 2-way |
| Delivery form | Without frame |
| Rated current | 10 AX - 250 V AC |
| Rocker color | Aluminium |
| Kind of terminals | Screwless terminals |

Complementary

| | |
|--------------------------------|-----------------------------------------------------------|
| Accessory / separate part type | Claw and screw for mechanism |
| Power range | 2300 W |
| Installation | Flush |
| Terminal capacity | 2 x 2.5 mm ² |
| Wire structure | Flexible Rigid |
| Wire stripping length | 13 mm |
| Material of visible parts | Thermoplastic ABS-UV stabilised |
| Surface finish | Glossy |
| Fixing mode | Claws, span of claws working range : 51...70 mm Screws |
| Height | 71 mm |
| Width | 71 mm |
| Depth | 37 mm |
| Depth of visual part | 12 mm |
| Product weight | 0.055042 kg |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

| | |
|-------------------------|-------------|
| Standards | IEC 60669-1 |
| Conformity mark | CE |
| Product certifications | GOST-R |
| IP degree of protection | IP20 |

Offer Sustainability

| | |
|----------------------------------|------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available Product Environmental Profile |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|