



ⓘ Discontinued

### Commercial status

Discontinued: 12 April 2019

has not been replaced. Please contact your customer care center for more information.

### Main

Range name	Sedna
Range	Sedna
Device application	Control
Product or component type	Switch
Function	1-pole 2-way
Delivery form	Without frame
Rated current	10 AX at 250 V AC
Rocker color	Titanium
Kind of terminals	Screwless terminals

### Complementary

Accessory / separate part type	Claw and screw for mechanism
Pilot light	Red indicator lamp
Power range	2300 W
Installation	Flush
Terminal capacity	2 cable(s) 2.5 mm <sup>2</sup>
Wire structure	Flexible Rigid
Wire stripping length	13 mm
Material of visible parts	Thermoplastic ABS-UV stabilised
Surface finish	Glossy
Fixing mode	Claws, span of claws working range: 51...70 mm Screws
Height	71 mm
Width	71 mm
Depth	37 mm
Depth of visual part	12 mm
Net weight	0.059995 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Standards	IEC 60669-1
Conformity mark	CE
Product certifications	GOST-R
IP degree of protection	IP20

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------