



Main

Range name	Sedna
Range	Sedna
Device application	Control
Product or component type	Push-button
Function	1-pole 2-way push-button
Delivery form	Without frame
Rated current	10 A - 250 V AC
Rocker color	Aluminium
Marking	Without marking
Kind of terminals	Screwless terminals

Complementary

Accessory / separate part type	Claw and screw for mechanism
Power range	2300 W
Installation	Flush
Terminal capacity	2 x 2.5 mm ²
Wire structure	Flexible Rigid
Wire stripping length	13 mm
Material of visible parts	Thermoplastic ABS-UV stabilised
Surface finish	Glossy
Fixing mode	Claws, span of claws working range : 51...70 mm Screws
Height	71 mm
Width	71 mm
Depth	37 mm
Depth of visual part	12 mm
Product weight	0.055251 kg

Environment

Standards	IEC 60669-1
Conformity mark	CE
Product certifications	GOST-R
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1715 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------