



### Main

Range name	Sedna
Range	Sedna
Device application	Control
Product or component type	Switch
Function	Intermediate
Delivery form	Without frame
Rated current	10 AX - 250 V AC
Rocker color	White
Kind of terminals	Screwless terminals

### Complementary

Accessory / separate part type	Claw and screw for mechanism
Power range	2300 W
Installation	Flush
Terminal capacity	2 x 2.5 mm <sup>2</sup>
Wire structure	Flexible Rigid
Wire stripping length	13 mm
Material of visible parts	Thermoplastic ABS-UV stabilised
Surface finish	Glossy
Fixing mode	Claws, span of claws working range : 51...70 mm Screws
Height	71 mm
Width	71 mm
Depth	37 mm
Depth of visual part	12 mm
Product weight	0.066242 kg

## Environment

Standards	IEC 60669-1
Conformity mark	CE
Product certifications	GOST-R
IP degree of protection	IP20

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------