



### Main

Range name	Sedna
Product or component type	Push-button
Delivery form	Complete product
Kind of terminals	Screwless terminals
Cover plate color	Cream
Function	1-pole push-button
Rated current	10 A - 250 V AC

### Complementary

Installation	Flush
Height	80 mm
Material of visible parts	Thermoplastic ABS-UV stabilised
Power range	2300 W
Product weight	0.0855 kg
Depth of visual part	12 mm
Wire structure	Flexible Rigid
Depth	37 mm
Surface finish	Glossy
Width	85 mm
Wire stripping length	13 mm
Fixing mode	Screws or claws, 51...70 mm
Terminal capacity	2 x 2.5 mm <sup>2</sup>

### Environment

IP degree of protection	IP20
Conformity mark	CE

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------