



Main

| | |
|---------------------------|---------------------|
| Range name | Sedna |
| Product or component type | Push-button |
| Delivery form | Complete product |
| Marking | Bell symbol |
| Kind of terminals | Screwless terminals |
| Cover plate color | White |
| Function | 1-pole push-button |
| Rated current | 10 A - 250 V AC |

Complementary

| | |
|---------------------------|---------------------------------|
| Installation | Flush |
| Height | 85 mm |
| Material of visible parts | Thermoplastic ABS-UV stabilised |
| Power range | 2300 W |
| Product weight | 0.0905 kg |
| Depth of visual part | 12 mm |
| Wire structure | Flexible Rigid |
| Depth | 37 mm |
| Surface finish | Glossy |
| Width | 85 mm |
| Wire stripping length | 13 mm |
| Fixing mode | Screws or claws, 51...70 mm |
| Terminal capacity | 2 x 2.5 mm ² |

Environment

| | |
|-------------------------|------|
| IP degree of protection | IP44 |
|-------------------------|------|

| | |
|-----------------|----|
| Conformity mark | CE |
|-----------------|----|

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1002 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
