



Main

Range name	Sedna
Range	Sedna
Product or component type	Push-button
Function	Double 1-pole
Delivery form	Without frame
Type of packing	Flow-pack and cardboard with eurohole
Rated current	10 A - 250 V AC
Rocker color	Graphite
Marking	Without marking
Kind of terminals	Screwless terminals

Complementary

Power range	2300 W
Installation	Flush
Terminal capacity	2 x 2.5 mm ²
Wire structure	Flexible Rigid
Wire stripping length	13 mm
Material of visible parts	Thermoplastic ABS-UV stabilised
Surface finish	Glossy
Fixing mode	Claws, span of claws working range : 51...70 mm Screws
Height	71 mm
Width	71 mm
Depth	37 mm
Depth of visual part	12 mm
Product weight	0.07061 kg

Environment

Standards	IEC 60669-1
Conformity mark	CE
Product certifications	GOST-R
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1715 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations