



### Main

Range name	Sedna
Product or component type	Push-button
Function	Roller blind
Delivery form	Complete product
Type of packing	Blister
Rated current	10 A - 250 V AC
Cover plate color	Aluminium
Kind of terminals	Screwless terminals

### Complementary

Installation	Flush
Interlocking type	Electrical
Power range	2300 W
Terminal capacity	2 x 2.5 mm <sup>2</sup>
Wire structure	Flexible Rigid
Wire stripping length	13 mm
Material of visible parts	ASA + PC
Surface finish	Glossy
Fixing mode	Screws or claws, span of claws working range : 51...70 mm
Height	80 mm
Width	85 mm
Depth	37 mm
Depth of visual part	12 mm
Product weight	0.070874 kg

## Environment

Conformity mark	CE
IP degree of protection	IP20

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1152 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations