



### Main

|                   |                   |
|-------------------|-------------------|
| Function          | Presence detector |
| Delivery form     | Without frame     |
| Cover plate color | Cream             |

### Complementary

|                            |                                 |
|----------------------------|---------------------------------|
| Power range                | 2300 W                          |
| Rated current              | 10 A - 230 V AC 50 Hz           |
| Light intensity adjustment | 5...1000 lux                    |
| Time delay                 | <= 20 minutes                   |
| Kind of terminals          | Pillar terminals                |
| Terminal capacity          | 1 x 2.5 mm <sup>2</sup>         |
| Wire structure             | Rigid<br>Flexible               |
| Wire stripping length      | 8 mm                            |
| Installation               | Flush                           |
| Fixing mode                | Screws                          |
| Material of visible parts  | Thermoplastic ABS-UV stabilised |
| Surface finish             | Glossy                          |
| Height                     | 71 mm                           |
| Width                      | 71 mm                           |
| Depth                      | 51.4 mm                         |
| Product weight             | 0.09741 kg                      |
| Depth of visual part       | 26.6 mm                         |

### Environment

|                         |        |
|-------------------------|--------|
| Conformity mark         | CE     |
| IP degree of protection | IP20   |
| Product certifications  | GOST-R |

### Offer Sustainability

|                        |   |
|------------------------|---|
| RoHS (date code: YYWW) | Compliant - since 1409 - Schneider Electric declaration of conformity |
|------------------------|---|

---

REACH

Reference not containing SVHC above the threshold  
Reference not containing SVHC above the threshold

---

**Contractual warranty**

---

Warranty period

18 months

---