



Main

Range name	Sedna
Function	Presence detector
Delivery form	Complete product
Rated current	10 A - 230 V AC 50 Hz
Cover plate color	Aluminium
Kind of terminals	Pillar terminals

Complementary

Installation	Flush
Power range	2300 W
Light intensity adjustment	5...1000 lux
Time delay	<= 20 minutes
Terminal capacity	1 x 2.5 mm ²
Wire structure	Rigid Flexible
Wire stripping length	8 mm
Material of visible parts	Thermoplastic ABS-UV stabilised
Surface finish	Glossy
Fixing mode	Screws
Height	80 mm
Width	85 mm
Depth	51.4 mm
Depth of visual part	26.6 mm
Product weight	0.116 kg

Environment

Conformity mark	CE
IP degree of protection	IP20

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1002 - Schneider Electric declaration of conformity
------------------------	---

Contractual warranty

Warranty period	18 months
-----------------	-----------
