



Main

Range name	Sedna
Function	Push-button dimmer
Function	2-way
Delivery form	Without frame
Cover plate color	Graphite
Kind of terminals	Pillar terminals

Complementary

Installation	Flush
Dimmer application	Capacitive load Resistive load
Load type	230 V AC halogen lamp 25...325 W Low voltage halogen lamp with electronic transformer 25...325 VA 230 V AC incandescent lamp 25...325 W
Rated voltage	230 V AC
Protection type	Electronic fuse protection
Terminal capacity	1 x 2.5 mm ²
Wire structure	Flexible Rigid
Wire stripping length	7 mm
Material of visible parts	Thermoplastic ABS-UV stabilised
Surface finish	Glossy
Fixing mode	Claws, span of claws working range : 51...80 mm Screws
Height	71 mm
Width	71 mm
Depth	47.5 mm
Depth of visual part	20 mm
Product weight	0.10667 kg

Environment

Standards	EN 60669-2-1
-----------	--------------

Conformity mark	CE
Product certifications	GOST-R
IP degree of protection	IP20

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1601 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold