



### Main

Range name	Sedna
Function	Socket-outlet
Delivery form	Without frame
Outlet poles configuration	2P
Outlet standard description	Without earthing contact
Outlet standard	Poland
Rated current	16 A - 250 V AC
Cover plate color	White
Kind of terminals	Screwless terminals

### Complementary

Installation	Flush
Power range	3680 W
Terminal capacity	2 x 2.5 mm <sup>2</sup>
Wire structure	Flexible Rigid
Wire stripping length	13 mm
Material of visible parts	ASA + PC
Surface finish	Glossy
Fixing mode	Screws 52...69 mm Claws, span of claws working range :
Height	71 mm
Width	71 mm
Depth	38.3 mm
Depth of visual part	10 mm
Product weight	0.055616 kg

### Environment

Standards	IEC 60884-1
Product certifications	GOST-R
IP degree of protection	IP20