



Main

Range name	Sedna
Function	Socket-outlet
Delivery form	Without frame
Outlet poles configuration	2P + E
Outlet standard description	Side earth
Outlet standard	Poland
Rated current	16 A - 250 V AC
Cover plate color	Aluminium
Kind of terminals	Screwless terminals

Complementary

Installation	Flush
Power range	3680 W
Terminal capacity	2 x 2.5 mm ²
Wire structure	Flexible Rigid
Wire stripping length	13 mm
Material of visible parts	PC
Surface finish	Glossy
Fixing mode	Screws 52...69 mm Claws, span of claws working range :
Height	71 mm
Width	71 mm
Depth	41.3 mm
Depth of visual part	10 mm
Product weight	0.06214 kg

Environment

Standards	IEC 60884-1
Product certifications	GOST-R
IP degree of protection	IP20