



Main

Range name	Sedna
Function	Socket-outlet
Delivery form	Without frame
Outlet poles configuration	2P + E with shutters
Outlet standard description	Side earth
Rated current	16 A - 250 V AC
Cover plate color	Beige
Kind of terminals	Screw terminals
Colour code	RAL 1013

Complementary

Installation	Flush
Power range	3680 W
Terminal capacity	2 x 2.5 mm ²
Wire structure	Flexible Rigid
Wire stripping length	13 mm
Material of visible parts	ASA + PC
Surface finish	Glossy
Fixing mode	Screws 52...69 mm By screws and claws, span of claws working range :
Height	71 mm
Width	71 mm
Depth	47.3 mm
Depth of visual part	16 mm
Product weight	0.073818 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 60884-1
Product certifications	GOST-R
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1715 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------