



### Main

Range	Sedna
Product or component type	Socket-outlet
Outlet standard description	Side earth
Delivery form	Complete product
Additional features	Lid and shuttered
Rated current	16 A - 250 V AC
Cover plate color	Cream
Kind of terminals	Lift terminals

### Complementary

Installation	Flush
Power range	3680 W
Terminal capacity	2 x 2.5 mm <sup>2</sup>
Wire structure	Flexible Rigid
Wire stripping length	13 mm
Material of visible parts	ASA + PC
Surface finish	Glossy
Fixing mode	Screws or claws, 52...69 mm
Height	80 mm
Width	85 mm
Depth	47.3 mm
Depth of visual part	16 mm
Product weight	0.074818 kg

### Environment

IP degree of protection	IP20
-------------------------	------

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1715 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------