



### Main

Range	Sedna
Function	TV socket
Device application	Media device support
Delivery form	Mechanism with central plate
TV socket type	Intermediate socket (passage)
Device composition	Support ring
Cover plate color	Titanium

### Complementary

TV connector type	1 x male IEC 9.52 mm
Number of outputs	1
Through loss	8 dB
Attenuation	8 dB for TV signal for 5...862 MHz frequency
Connections - terminals	Screw terminals
Material of visible parts	Thermoplastic ABS-UV stabilised
Kind of terminals	Glossy
Installation	Flush
Fixing mode	Claws, span of claws working range : 51...80 mm Screws
Height	70 mm
Width	64 mm
Depth	40 mm
Depth of visual part	14.6 mm
Product weight	0.07701 kg

### Environment

Conformity mark	CE
IP degree of protection	IP20
Environmental health and issues	Halogen free

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1125 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------