



Main

Range	Sedna
Function	TV/SAT socket
Delivery form	Without frame
TV socket type	Intermediate socket (passage)
Cover plate color	Cream

Complementary

TV connector type	1 x male IEC 9.52 mm
SAT connector type	1 x F type
Number of outputs	2
Through loss	4 dB
Attenuation	4 dB for TV signal for 5...862 MHz frequency 3 dB for SAT signal for 950...2400 MHz frequency
Connections - terminals	Screw terminals
Material of visible parts	Thermoplastic ABS-UV stabilised
Kind of terminals	Glossy
Installation	Flush
Fixing mode	Claws, span of claws working range : 55...70 mm Screws
Height	70 mm
Width	64 mm
Depth	40.5 mm
Depth of visual part	17.4 mm
Product weight	0.10264 kg

Environment

Conformity mark	CE
-----------------	----

IP degree of protection	IP20
-------------------------	------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0946 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------
