



### Main

Range	Sedna
Function	TV/SAT/R socket
Delivery form	Without frame
TV socket type	Intermediate socket (passage)
Cover plate color	White

### Complementary

TV connector type	1 x male IEC 9.52 mm
FM connector type	1 x female IEC
SAT connector type	1 x F type
Number of outputs	3
Through loss	8 dB
Attenuation	3 dB for SAT signal for 950...2400 MHz frequency 8 dB for TV signal for 5...862 MHz frequency 10 dB for R signal for 88...125 MHz frequency
Connections - terminals	Screw terminals
Material of visible parts	Thermoplastic ABS-UV stabilised
Kind of terminals	Glossy
Installation	Flush
Fixing mode	Claws, span of claws working range : 55...70 mm Screws
Height	70 mm
Width	64 mm
Depth	40.5 mm
Depth of visual part	17.4 mm
Product weight	0.10893 kg

## Environment

Conformity mark	CE
IP degree of protection	IP20

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0946 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------