



Main

Range	Sedna
Function	TV/SAT socket
Delivery form	Without frame
TV socket type	End-of-line (terminal socket)
Cover plate color	Titanium

Complementary

TV connector type	1 x male IEC 9.52 mm
SAT connector type	2 x F type
Number of outputs	3
Through loss	1 dB
Attenuation	1 dB for TV signal for 5...862 MHz frequency 1 dB for SAT1 signal for 5...2400 MHz frequency 1 dB for SAT2 signal for 950...2400 MHz frequency
Connections - terminals	Screw terminals
Material of visible parts	Thermoplastic ABS-UV stabilised
Kind of terminals	Glossy
Installation	Flush
Fixing mode	Claws, span of claws working range : 55...70 mm Screws
Height	70 mm
Width	64 mm
Depth	40.5 mm
Depth of visual part	17.4 mm
Product weight	0.11307 kg

Environment

Conformity mark	CE
IP degree of protection	IP20

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1126 - Schneider Electric declaration of conformity
------------------------	---

 Schneider Electric declaration of conformity

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
-------	--

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------
