



### Main

Range	Sedna
Function	Telephone + data outlet
Delivery form	Without frame
Telephone socket type	RJ11
Data connector type	RJ45 category 5e UTP
Cover plate color	Titanium

### Complementary

Wire structure	Rigid
Kind of terminals	IDC : RJ45 Screw terminals : RJ11
Material of visible parts	Thermoplastic ABS-UV stabilised
Surface finish	Glossy
Installation	Flush
Fixing mode	Claws, span of claws working range : 48...81 mm Screws
Height	71 mm
Width	71 mm
Depth	36 mm
Depth of visual part	14.5 mm
Product weight	0.05881 kg

### Environment

IP degree of protection	IP20
-------------------------	------

### Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant - since 0946 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------