



Main

Range	Sedna
Function	Telephone + data outlet
Delivery form	Complete product
Telephone socket type	RJ11
Data connector type	RJ45 - category 5e U/UTP
Cover plate colour tint	Cream

Complementary

Kind of terminals	IDC
Wire structure	Rigid
Material of visible parts	Thermoplastic ABS-UV stabilised
Surface finish	Glossy
Device mounting	Flush
Fixing mode	Screws or claws, 48...81 mm
Height	80 mm
Width	85 mm
Depth	36 mm
Depth of visual part	14.5 mm
Product weight	0.0715 kg


Environment

IP degree of protection	IP20
-------------------------	------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1002 - Schneider Electric declaration of conformity

 [Schneider Electric declaration of conformity](#)

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available  Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------