



Main

Range	Sedna
Function	Telephone + data outlet
Delivery form	Without frame
Telephone socket type	RJ11
Data connector type	RJ45 category 6 UTP
Cover plate color	Aluminium

Complementary

Wire structure	Rigid
Kind of terminals	IDC : RJ45 Screw terminals : RJ11
Material of visible parts	Thermoplastic ABS-UV stabilised
Surface finish	Glossy
Installation	Flush
Fixing mode	Claws, span of claws working range : 48...81 mm Screws
Height	71 mm
Width	71 mm
Depth	36 mm
Depth of visual part	14.5 mm
Product weight	0.05744 kg

Environment

IP degree of protection	IP20
-------------------------	------

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant - since 0946 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------