



### Main

Range name	Sedna
Function	Loudspeaker socket
Delivery form	Without frame
Cover plate color	White
Kind of terminals	Screwless terminals
Colour code	RAL 9003

### Complementary

Installation	Flush
Socket number	2
Fixing of mechanism	Screws and claws
Terminal capacity	1 x 1.5 mm <sup>2</sup>
Wire structure	Flexible Rigid
Wire stripping length	7 mm
Material of visible parts	Thermoplastic ABS-UV stabilised
Surface finish	Glossy
Fixing mode	Claws, span of claws working range : 51...70 mm Screws
Height	71 mm
Width	71 mm
Depth	44.5 mm
Depth of visual part	24.7 mm
Product weight	0.0592 kg

### Environment

IP degree of protection	IP20
-------------------------	------

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
------------------------	---

---

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---