


Product data sheet

Specifications



Sedna - room thermostat with cooling mode - 10A cream

SDN6001123

 **Discontinued on:** Dec 31, 2016

 **Discontinued**

Main

Range Name	Sedna
Range	Sedna
Function	Thermostat
Device Application	Room
Delivery Form	Complete product
Technology Type	Electromechanical

Complementary

Colour Tint	Cream
Rated Current	10 A at 230 V AC 50 Hz 5 A
Power Range	2200 W 1100 W
Measurement Accuracy	0.5 °C
Terminal Capacity	2 cable(s) 2.5 mm²
Wire Structure	Flexible Stranded with sleeve Rigid
Wire Stripping Length	10 mm
Kind Of Terminals	Pillar terminals
Temperature Setting Range	5...30 °C
Material Of Visible Parts	Thermoplastic ABS-UV stabilised
Surface Finish	Glossy
Installation	Flush
Fixing Mode	Screws
Height	80 mm
Width	85 mm
Depth	48 mm
Depth Of Visual Part	25.4 mm
Net Weight	0.082 kg

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP20
Conformity Mark	CE
Product Certifications	GOST-R
Standards	EN 60730-2-9

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	8.5 cm
Package 1 Length	4.8 cm
Package 1 Weight	82 g

Contractual warranty

Warranty	18 months
----------	-----------