


Product data sheet

Specifications



servo motor SH3 070
2,94Nm,nokey,multi,brake,str.conn,I
P65/IP67,8k RPM

SH30703M02F1200

Main

Range Compatibility	PacDrive 3
Product Or Component Type	Servo motor
Device Short Name	SH3.....M

Complementary

Maximum Mechanical Speed	8000 rpm
[Us] Rated Supply Voltage	115...480 V
Network Number Of Phases	Three phase
Continuous Stall Current	2.1 A
Continuous Stall Torque	2.94 N.m at 115...480 V three phase
Continuous Power	830 W
Peak Stall Torque	11.3 N.m at 115...480 V three phase
Nominal Output Power	240 W at 115 V single phase 460 W at 230 V single phase 880 W at 400 V three phase 1030 W at 480 V three phase
Nominal Torque	3.05 N.m at 115 V single phase 2.95 N.m at 230 V single phase 2.63 N.m at 400 V three phase 2.63 N.m at 480 V three phase
Nominal Speed	750 rpm at 115 V single phase 1500 rpm at 230 V single phase 3000 rpm at 400 V three phase 3600 rpm at 480 V three phase
Maximum Current Irms	8.7 A
Shaft End	Smooth shaft
Shaft Diameter	14 mm
Shaft Length	30 mm
Key Width	5 mm
Ip Degree Of Protection	IP65 motor: conforming to IEC 60034-5 IP65 shaft bushing: conforming to IEC 60034-5 IP67 housing: conforming to IEC 60034-5
Encoder Type	Absolute multiturn SinCos Hiperface
Speed Feedback Resolution	128 periods
Holding Brake	With
Holding Torque	3 N.m
Mounting Support	International standard flange

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Motor Flange Size	70 mm
Electrical Connection	Rotatable right angled connector
Torque Constant	1.4 N.m/A at 120 °C
Back Emf Constant	95 V/krpm at 20 °C
Number Of Motor Poles	3
Rotor Inertia	0.807 kg.cm²
Stator Resistance	10.7 Ohm
Stator Inductance	76.85 mH
Maximum Radial Force Fr	730 N at 1000 rpm 580 N at 2000 rpm 510 N at 3000 rpm 460 N at 4000 rpm 430 N at 5000 rpm 400 N at 6000 rpm
Maximum Axial Force Fa	80 N
Type Of Cooling	Natural convection
Length	254 mm
Centring Collar Diameter	60 mm
Centring Collar Depth	2.5 mm
Number Of Mounting Holes	4
Mounting Holes Diameter	5.5 mm
Circle Diameter Of The Mounting Holes	82 mm
Net Weight	3.8 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------