



### Overview

Model Name	APC Smart-UPS 2200VA LCD 120V
Includes	CD with software , Documentation CD , Smart UPS signalling RS-232 cable , USB cable
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Colombia , Costa Rica , Dominican Republic , Ecuador , El Salvador , Guadeloupe , Guatemala , Honduras , Mexico , Nicaragua , Panama , Puerto Rico

### Output

Output Power Capacity	1920 Watts / 1920 VA
Max Configurable Power (Watts)	1980 Watts / 2200 VA
Nominal Output Voltage	120V
Output Voltage Distortion	Less than 5%
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Output Frequency (sync to mains)	Line Interactive
Waveform Type	Sine wave
Output Connections	(2) NEMA 5-20R (Battery Backup) , (8) NEMA 5-15R (Battery Backup)

### Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA 5-20P
Cord Length	1,83 meters
Input voltage range for main operations	82 - 144 V
Input voltage adjustable range for mains operation	75 - 154V

### Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Typical recharge time	3 hour(s)
Replacement Battery	RBC55
RBC Quantity	1

## Communications & Management

Interface Port(s)	SmartSlot , USB
Available SmartSlot™ Interface Quantity	1
Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Emergency Power Off (EPO)	Yes

## Surge Protection and Filtering

Surge energy rating	530 Joules
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

## Physical

Maximum Height	432.0 mm
Maximum Width	196.0 mm
Maximum Depth	544.0 mm
Net Weight	50.91 kg
Shipping Weight	60.91 kg
Shipping Height	559.0 mm
Shipping Width	381.0 mm
Shipping Depth	762.0 mm
Color	Black
SCC Codes	0073130426869 7
Units per Pallet	9.0

## Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	45.000 dB
Online Thermal Dissipation	275.000 BTU/hr

## Conformance

Approvals	CSA , FCC Part 15 Class A , UL 1778
Standard warranty	3 years repair or replace (excluding battery) and 2 year for battery , optional extended warranties available , optional on-site warranties available
Equipment protection policy	Lifetime : \$150000

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs