



Main

Product or component type	Uninterruptible power supply (UPS)
Provided equipment	1 USB software CD 1 RS232 USB cable 1 user manual
Mounting support	Floor-standing
Communication port protocol	USB RS232
Function available	Intelligent charging algorithm monitors battery and AC supply Battery monitoring Audible alarm when a fault condition arises Internal bypass Optional communication kit for remote monitoring
Topology	Line interactive

Complementary

Display type	LCD display
Integrated connection type	USB port RS232
Type of signal	Sine wave
Protection device type	Surge protection device (SPD) Miniature circuit breaker (MCB)
Protection type	Surge arrester Fuse
Input voltage	230 V AC 220 V AC 240 V AC
Output voltage	230 V AC nominal mode 220 V AC 240 V AC
IP degree of protection	IP20
Transfer time	6 ms
Network frequency	44...66 Hz
Power range	2000 VA
Electrical connection	Output: 6 outlet IEC 320 C13 Input: 1 inlet IEC 320 C14
Local signalling	Alarm, distinctive for low battery

LCD display, continuous or intermittent tone for overload
LCD display for status and alert

Battery type	Lead-acid battery Sealed rechargeable Internal battery
Number of batteries	4
Charging time	6 h
Battery voltage	12 V
Battery capacity	7 Ah
Battery life	5 year(s)
Quantity per set	Set of 1
Net weight	23.5 kg
Height	240 mm
Width	180 mm
Depth	455 mm

Environment

Acoustic level	< 45 dBA
Relative humidity	0...95 %, non-condensing
Operating altitude	0...3000 m
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-10...40 °C
Product certifications	CE

Contractual warranty

Warranty	2 years
----------	---------