



Overview

Model Name	APC Easy UPS SRV 10000VA 230V
Includes	CD with software , USB cable , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Angola , Armenia , Austria , Azerbaijan , Belarus , Belgium , Benin , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Cambodia , Cameroon , Central African Republic , Chad , Chile , Colombia , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Croatia , Cyprus , Czech Republic , Denmark , Dominica , East Timor , Estonia , Finland , France , Gabon , Gambia , Georgia , Germany , Gibraltar , Greece , Guadeloupe , Guinea , French Guiana , Hong Kong , Hungary , Iceland , Indonesia , Iraq , Ireland , Israel , Italy , Jordan , Kazakhstan , KOREA, REPUBLIC OF , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Madagascar , Malawi , Malaysia , Malta , Martinique , Mauritania , Mauritius , Moldova, Republic Of , Mongolia , Morocco , Myanmar , Namibia , Netherlands , Netherlands Antilles , Niger , Norway , Pakistan , Paraguay , Peru , Philippines , Poland , Portugal , Romania , Russian Federation , SAINT LUCIA , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Spain , Sweden , Switzerland , Tajikistan , Thailand , Togo , Tunisia , Turkey , Turkmenistan , Ukraine , Uruguay , Uzbekistan , Viet Nam , Western Sahara , Zambia , Zimbabwe

Output

Output Power Capacity	10.0 KW / 10.0 kVA
Max Configurable Power (Watts)	10.0 KW / 10.0 kVA
Nominal Output Voltage	230V
Other Output Voltages	220, 240V
Crest Factor	3 : 1
Crest Factor	Double Conversion Online
Waveform Type	Sine wave

Input

Nominal Input Voltage	230V
Input Frequency	40 - 70 Hz
Input Connections	Hard Wire 3-wire
Other Input Voltages	220 , 240

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Typical recharge time	3 hour(s)

Communications & Management

Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Emergency Power Off (EPO)	Yes

Surge Protection and Filtering

Surge energy rating	600 Joules
---------------------	------------

Physical

Maximum Height	685.0 mm
Maximum Width	190.0 mm
Maximum Depth	447.0 mm
Net Weight	65.0 kg
Shipping Weight	77.0 kg
Shipping Height	910.0 mm
Shipping Width	320.0 mm
Shipping Depth	580.0 mm

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 (non-condensing) %
Operating Elevation	0-3000 meters
Storage Relative Humidity	0 - 95 (non-condensing) %
Storage Elevation	0-14763.6 meters
Audible noise at 1 meter from surface of unit	0.000 dB

Conformance

Approvals	CE , IEC 62040-1-1 , IEC 62040-1-2
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs