



Main

Product or component type	Battery
Provided equipment	Documentation CD User manual
Battery capacity	9 Ah
Number of cables	1
Battery type	Lead-acid battery VRLA
Battery voltage	36 V
Mounting mode	Floor-standing

Complementary

Range of product	Easy UPS 1Ph On-Line
Type of installation	Indoor
Quantity per set	6 pieces
Net weight	19.6 kg
Height	23.8 cm
Width	14.5 cm
Depth	40 cm

Environment

IP degree of protection	IP20
Product certifications	CE
Ambient air temperature for storage	-15...40 °C
Relative humidity	0...95 % non-condensing

Contractual warranty

Warranty	2 years
----------	---------