



Overview

Model Name	APC Smart-UPS XL 1000VA USB & Serial 230V No Battery For China
Includes	CD with software , Smart UPS signalling RS-232 cable , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	China

Output

Output Power Capacity	800 Watts / 1000 VA
Max Configurable Power (Watts)	800 Watts / 1000 VA
Nominal Output Voltage	230V
Output Voltage Note	Configurable for 220 : 230 or 240 nominal output voltage
Output Voltage Distortion	Less than 5% at full load
Output Frequency (sync to mains)	47 - 53 Hz for 50 Hz nominal , 57 - 63 Hz for 60 Hz nominal
Output Frequency (sync to mains)	Line Interactive
Waveform Type	Sine wave
Output Connections	(2) IEC Jumpers (Battery Backup) , (8) IEC 320 C13 (Battery Backup)

Input

Nominal Input Voltage	230V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	IEC-320 C14
Cord Length	1.83 meters
Input voltage range for main operations	160 - 285 V
Input voltage adjustable range for mains operation	151 - 302V

Batteries & Runtime

Battery Type	No internal battery - uses external battery system
--------------	--

Communications & Management

Interface Port(s)	DB-9 RS-232 , SmartSlot , USB
-------------------	-------------------------------

Available SmartSlot™ Interface Quantity	1
Control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : and Overload Indicators
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Emergency Power Off (EPO)	Optional

Surge Protection and Filtering

Surge energy rating	480 Joules
Filtering	Full time multi-pole noise filtering : 0.7% IEEE surge let-through : zero clamping response time : meets UL 1449

Physical

Maximum Height	216.0 mm
Maximum Width	170.0 mm
Maximum Depth	439.0 mm
Net Weight	12.91 kg
Shipping Weight	15.0 kg
Shipping Height	381.0 mm
Shipping Width	330.0 mm
Shipping Depth	584.0 mm
Color	Black
Units per Pallet	24.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	42.000 dB
Online Thermal Dissipation	120.000 BTU/hr

Conformance

Standard warranty	2 years repair or replace
-------------------	---------------------------

Sustainable Offer Status

RoHS	Compliant
Other Environmental Compliance	China RoHS