



Overview

Model Name	APC Smart-UPS & serial 230V, India specific
Includes	CD with software , Smart UPS signalling RS-232 cable , USB cable , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Bangladesh , India , Nepal , Sri Lanka

Output

Output Power Capacity	980 Watts / 1500 VA
Max Configurable Power (Watts)	980 Watts / 1500 VA
Nominal Output Voltage	230V
Output Voltage Note	Configurable for 220 : 230 or 240 nominal output voltage
Output Voltage Distortion	Less than 5%
Output Frequency (sync to mains)	47 - 53 Hz for 50 Hz nominal , 57 - 63 Hz for 60 Hz nominal
Output Frequency (sync to mains)	Line Interactive
Waveform Type	Sine wave
Output Connections	(2) IEC Jumpers (Battery Backup) , (8) IEC 320 C13 (Battery Backup)

Input

Nominal Input Voltage	230V
Input Frequency	50 Hz +/- 3 Hz
Input Connections	IEC-320 C14
Input voltage range for main operations	160 - 286 V
Input voltage adjustable range for mains operation	151 - 302V

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Typical recharge time	3 hour(s)
RBC Quantity	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Communications & Management

Interface Port(s)	DB-9 RS-232 , SmartSlot , USB
Control panel	LED status display with On Line : On Battery : Replace Battery and Overload indicators

Surge Protection and Filtering

Surge energy rating	480 Joules
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Physical

Maximum Height	216.0 mm
Maximum Width	170.0 mm
Maximum Depth	439.0 mm
Net Weight	24.09 kg
Shipping Weight	26.82 kg
Shipping Height	370.0 mm
Shipping Width	330.0 mm
Shipping Depth	590.0 mm
Units per Pallet	24.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 40 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	45.000 dB
Online Thermal Dissipation	135.000 BTU/hr

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs