



Overview

Model Name	APC Smart-UPS 3000VA USB & Serial 230V, India specific
Includes	CD with software , USB cable , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Bangladesh , India , Nepal , Sri Lanka

Output

Output Power Capacity	2700 Watts / 3000 VA
Max Configurable Power (Watts)	2700 Watts / 3000 VA
Nominal Output Voltage	230V
Output Voltage Note	Configurable for 220 : 230 or 240 nominal output voltage
Output Voltage Distortion	Less than 5%
Output Frequency (sync to mains)	47 - 53 Hz for 50 Hz nominal , 57 - 63 Hz for 60 Hz nominal
Output Frequency (sync to mains)	Line Interactive
Waveform Type	Sine wave
Output Connections	(1) IEC 320 C19 (Battery Backup) , (2) IEC Jumpers (Battery Backup) , (8) IEC 320 C13 (Battery Backup)

Input

Nominal Input Voltage	230V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	British BS1363A , IEC-320 C20 , Schuko CEE 7/EU1-16P
Input voltage range for main operations	160 - 285 V
Input voltage adjustable range for mains operation	151 - 302V

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Typical recharge time	3 hour(s)
Replacement Battery	RBC55
RBC Quantity	1

Communications & Management

Interface Port(s)	DB-9 RS-232 , SmartSlot , USB
Control panel	LED status display with On Line : On Battery : Replace Battery and Overload indicators
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rating	365 Joules
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Physical

Maximum Height	432.0 mm
Maximum Width	196.0 mm
Maximum Depth	544.0 mm
Net Weight	55.91 kg
Shipping Weight	65.0 kg
Shipping Height	680.0 mm
Shipping Width	380.0 mm
Shipping Depth	760.0 mm
Units per Pallet	3.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	53.000 dB
Online Thermal Dissipation	375.000 BTU/hr

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs