



Overview

Model Name	APC Smart-UPS 750VA USB & Serial 230V, India Specific
Includes	CD with software , Smart UPS signalling RS-232 cable , USB cable , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Bangladesh , India , Nepal , Sri Lanka

Output

Output Power Capacity	500 Watts / 750 VA
Max Configurable Power (Watts)	500 Watts / 750 VA
Nominal Output Voltage	230V
Output Voltage Note	Configurable for 220 : 230 or 240 nominal output voltage
Output Voltage Distortion	Less than 5%
Output Frequency (sync to mains)	47 - 53 Hz for 50 Hz nominal , 57 - 63 Hz for 60 Hz nominal
Output Frequency (sync to mains)	Line Interactive
Waveform Type	Sine wave
Output Connections	(2) IEC Jumpers (Battery Backup) , (6) IEC 320 C13 (Battery Backup)

Input

Nominal Input Voltage	230V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	IEC-320 C14
Input voltage range for main operations	160 - 285 V
Input voltage adjustable range for mains operation	151 - 302V

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
--------------	--

Communications & Management

Interface Port(s)	DB-9 RS-232 , SmartSlot , USB
-------------------	-------------------------------

Physical

Maximum Height	157.0 mm
Maximum Width	137.0 mm
Maximum Depth	361.0 mm
Net Weight	13.18 kg
Shipping Weight	14.55 kg
Shipping Height	290.0 mm
Shipping Width	270.0 mm
Shipping Depth	500.0 mm
Units per Pallet	24.0

Environmental

Audible noise at 1 meter from surface of unit	0.000 dB
---	----------

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs