



Overview

Model Name	APC Smart-UPS 750VA RM 1U 100V USB and Serial
Includes	Rack Mounting brackets , Rack Mounting support rails , User Guide in Japanese
Standard Lead Time	Usually in Stock
Product Distribution	Japan

Output

Output Power Capacity	480 Watts / 750 VA
Max Configurable Power (Watts)	480 Watts / 750 VA
Nominal Output Voltage	100V
Output Voltage Distortion	Less than 5% at full load
Output Frequency (sync to mains)	47 - 53 Hz for 50 Hz nominal , 57 - 63 Hz for 60 Hz nominal
Output Frequency (sync to mains)	Line Interactive
Waveform Type	Sine wave
Output Connections	(4) NEMA 5-15R (Battery Backup)

Input

Nominal Input Voltage	100V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA 5-15P
Cord Length	2.44 meters
Maximum Input Current	10 A
Input Breaker Capacity	12 A

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Typical recharge time	3 hour(s)
Replacement Battery	RBC34L
RBC Quantity	1

Communications & Management

Interface Port(s)	DB-9 RS-232 , SmartSlot , USB
Available SmartSlot™ Interface Quantity	1
Control panel	--
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Emergency Power Off (EPO)	--

Physical

Maximum Height	44.0 mm
Maximum Width	483.0 mm
Maximum Depth	660.0 mm
Rack Height	1 U
Net Weight	21.8 kg
Shipping Weight	25.4 kg
Shipping Height	191.0 mm
Shipping Width	559.0 mm
Shipping Depth	775.0 mm
Color	Black
Units per Pallet	8.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	45.000 dB

Conformance

Approvals	UL 1778 , VCCI
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs